




Ballerina




Black




Buff



Chocolate




Dark Plum




Denim



Desert Sand




Dusty Rose



Forest



Haze



Light Sage




Maple




Mule



Mustard




Nickel



Olympic Beige




Pebble



Penny



Pewter



Port




Saddle




Seawater



Spa



Storm



Vanilla

| Construction        | Values                                              | Test Method   |
|---------------------|-----------------------------------------------------|---------------|
| Surface Composition | 100% Polyurethane<br>Hydro-Sil™ Silicone Protection |               |
| Backing Composition | 100% Polyester                                      | ASTM D 751-06 |
| Finished Width      | 54" Width                                           | ASTM D 751-06 |
| Railroaded          | No                                                  |               |
| Put-up              | 30 yards                                            |               |
| Stain Resistant     | Yes                                                 |               |
| Cleaning Code       | WS                                                  |               |

| Performance                          | Values                          | Test Method       |
|--------------------------------------|---------------------------------|-------------------|
| Adhesion                             | 4 lbs./in. × 4 lbs./in. min.    | ASTM D 751-06     |
| Grab Tensile                         | 50 lbs./in. × 50 lbs./in. min.  | ASTM D 751-06     |
| Trap Tear                            | 18 lbs./in. × 18 lbs./in. min.  | ASTM D 751-06     |
| Seam Strength                        | 40 lbs./in. × 40 lbs./in. min.  | ASTM D 751-06     |
| Stretch at 15# MD (warp) x CD (fill) | 10% x 20%                       | ASTM D 751-06     |
| Flex Resistance                      | 25,000 cycles                   | ASTM D 2097-91    |
| Blocking                             | No. 1 Pass                      | FTMS 191A-TM5872  |
| Crock Resistance                     | Wet – 4; Dry – 4                | AATCC 8-2007      |
| Wyzenbeek Abrasion                   | 100,000 cycles, #10 cotton duck | ASTM D 4157-13    |
| Hydrolysis Resistance                | 10 weeks                        | ISO 5423: 1992 E  |
| Colorfastness to Light               | 150 hours                       | ASTM D 4329-05    |
| Skin Sensitivity                     | Pass                            | ISO 10993-10:2021 |
| Skin Irritation                      | Pass                            | ISO 10993-23:2021 |

| Flammability                                   |      | Environmental                                                                              |
|------------------------------------------------|------|--------------------------------------------------------------------------------------------|
| California Technical Bulletin 117-2013, Sec. 1 | Pass | 1. No PolyVinyl Chloride, Plasticizers, Phalates, Stabilizers, Heavy Metals or Bisphenol A |
| I.M.O. A.652 (16) 8.2                          | Pass | 2. No flame retardants                                                                     |
| NFPA 260                                       | Pass | 3. No persistent organic pollutants                                                        |
| U.F.A.C. Class I                               | Pass | 4. RoHS and REACH compliance                                                               |
|                                                |      | 5. No toxic by-products                                                                    |
|                                                |      | 6. Water based, non-solvents technology                                                    |

## Suitable Applications Commercial

## Cleaning and Disinfecting

Remove ordinary dirt and smudges with mild soap and water. A 10:1 ratio of water to bleach solution may be used as a disinfectant. Rinse the surface with clean water after disinfecting. Dry with a soft, lint-free cloth or towel. We recommend that you use Clorox Healthcare and Clorox Pro products to disinfect Mitchell products in commercial settings.